



Appliance Oven Tubular

Appliance 15W E14 230-240V T22 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Main Application	Oven
Nominal Lifetime (Nom)	1000 h
Switching Cycle	4000X

Light Technical	
Luminous Flux (Nom)	90 lm
Luminous Flux (Rated) (Nom)	90 lm
Colour Temperature, horizontal (Nom)	2700 K
Colour Rendering Index horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	15.0 W
Lamp Current (Nom)	0.06 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1
Voltage (Nom)	230-240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear (CL)


Approval and Application	
Energy Efficiency Label	E
Energy Consumption kWh/1000 h	15 kWh

Product Data	
Full product code	872790094703800
Order product name	Appliance 15W E14 230-240V T22 CL OV 1CT
EAN/UPC - Product	8727900947038
Order code	94703800
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	921096244427
Net Weight (Piece)	12.000 g
ILCOS Code	IBT/C-15-230/240-E14-22*

Appliance Oven Tubular

Dimensional drawing

Product	D (max)	C (max)
Appliance 15W E14 230-240V T22 CL OV 1CT	22 mm	49 mm



APP 15W E14 230-240V T22 CL OV

