



# CLASSICTONE Lustre

## CLAS 25W B22 240V P45 CL 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear, white or inside-frosted glass bulb


### Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 h
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	200 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	CLAS 25W B22 240V P45 CL 1CT/10X10F
Full product name	CLAS 25W B22 240V P45 CL 1CT/10X10F
Full product code	871150002553150
Local code description	LCL25W240VC
Order code	921410545538
Material Nr. (12NC)	921410545538
Local order code	LCL25W240VC
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500025531
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500240965

CLASSICTONE Lustre

Dimensional drawing



Product	D	C (max)
CLAS 25W B22 240V P45 CL 1CT/10X10F	45 mm	71.5 mm

