



Standard Lustre P45 clear

Stan 25W E14 220-240V P45 CL 1CT/5X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base


Product data

| General Information | |
|-----------------------------|----------------------------------|
| Cap-Base | E14 [E14] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Luminous Flux | 210 lm |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 25 W |
| Voltage (Nom) | 220-240 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|--|
| Bulb Finish | Clear |
| Bulb Shape | P45 [P 45mm] |
| Product Data | |
| Order product name | Stan 25W E14 220-240V P45 CL 1CT/5X10F |
| Full product name | Stan 25W E14 220-240V P45 CL 1CT/5X10F |
| Full product code | 871829112396500 |
| Order code | 921411043301 |
| Material Nr. (12NC) | 921411043301 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500223449 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8718291123989 |

Standard Lustre P45 clear

Dimensional drawing



| Product | D | C (max) |
|--|-------|---------|
| Stan 25W E14 220-240V P45 CL 1CT/5X10F | 45 mm | 78 mm |

