



Standard Lustre P45 clear

Standard 40W E27 125-130V P45 CL 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	460 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	125-130 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	Stan 40W E27 125-130V P45 CL 1CT/10X10F
Full product name	Standard 40W E27 125-130V P45 CL 1CT/10X10F
Full product code	871016307607250
Order code	07607250
Material Nr. (12NC)	921421535673
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163076072
Numerator - Packs per outer box	100
EAN/UPC - Case	8710163077703

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Stan 40W E27 125-130V P45 CL 1CT/10X10F	45 mm	73 mm

