



# Standard Lustre P45 frosted

Stan 40W E27 220-240V P45 FR 1CT/5X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

## Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	385 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	Stan 40W E27 220-240V P45 FR 1CT/5X10F
Full product name	Stan 40W E27 220-240V P45 FR 1CT/5X10F
Full product code	871829112417700
Order code	921421643301
Material Nr. (12NC)	921421643301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500223364
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291124191

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
Stan 40W E27 220-240V P45 FR 1CT/5X10F	45 mm	73 mm

