

Standard Candle B35 clear

230V 25W CANDLE BC CLEAR

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base


Product data

| General Information | |
|-----------------------------|----------------------------------|
| Cap-Base | B22 [B22] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Luminous Flux | 205 lm |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 25 W |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|--------------------------|
| Bulb Finish | Clear |
| Bulb Shape | B35 [B 35mm] |
| Product Data | |
| Order product name | 230V 25W CANDLE BC CLEAR |
| Full product name | 230V 25W CANDLE BC CLEAR |
| Full product code | 890143700285300 |
| Order code | 921485544299 |
| Material Nr. (12NC) | 921485544299 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8901437002853 |
| Numerator - Packs per outer box | 300 |
| EAN/UPC - Case | 8727900076516 |

Standard Candle B35 clear

Dimensional drawing



| Product | D | C (max) |
|--------------------------|-------|---------|
| 230V 25W CANDLE BC CLEAR | 35 mm | 94.5 mm |

