



InfraRed Industrial Heat Incandescent

BR125 IR 150W E27 230-250V CL 1CT/10

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.


Product data

General Information	
Cap base	E27 [E27]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	5,000 h
Rated Lifetime (Hours)	5,000 h
Lighting Technology	Incandescent
Operating and Electrical	
Power Consumption	150 W
Voltage (nom.)	230-250 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear

Bulb material	Hard Glass
Bulb shape	BR125
Product Data	
Order product name	BR125 IR 150W E27 230-250V CL 1CT/10
Full product name	BR125 IR 150W E27 230-250V CL 1CT/10
Full EOC	871150057522725
Order code	57522725
Material no. (12 NC)	923211943801
Local order code	IR150CHHG
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500575227
Numerator – packs per outer box	10
EAN/UPC - Case	8727900209303

InfraRed Industrial Heat Incandescent

Dimensional drawing



Product	D	C (max)
BR125 IR 150W E27 230-250V CL 1CT/10	125 mm	173 mm

