



# InfraRed Industrial Heat Incandescent

## BR125 IR 250W E27 230-250V CL 1CT/10

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

### Product data

General Information	
Cap-Base	E27 [ E27]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Main Application	Infrared Industrial
Nominal Lifetime (Nom)	5000 h

Operating and Electrical	
Power (Rated) (Nom)	250 W
Voltage (Nom)	230-250 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear (CL)
Bulb Material	Hard Glass


Luminaire Design Requirements	
Bulb Temperature (Max)	500 °C

Product Data	
Full product code	871150057523425
Order product name	BR125 IR 250W E27 230-250V CL 1CT/10
EAN/UPC - Product	8711500575234
Order code	57523425
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	923212143801
Net Weight (Piece)	104.000 g

# InfraRed Industrial Heat Incandescent

## Dimensional drawing



Product	D	C (max)
BR125 IR 250W E27 230-250V CL 1CT/10	125 mm	173 mm

BR125 IR 250W E27 230-250V CL

