



InfraRed Industrial Heat Incandescent

BR125 IR 250W E27 230-250V CL 1CT/10


The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data

General Information		Bulb material	
Cap base	E27	Bulb material	Hard Glass
Operating position	UNIVERSAL [Any or Universal (U)]	Bulb shape	BR125
Nominal lifetime	5,000 h	Product Data	
Rated Lifetime (Hours)	5,000 h	Order product name	BR125 IR 250W E27 230-250V CL 1CT/10
Lighting Technology	Incandescent	Full product name	BR125 IR 250W E27 230-250V CL 1CT/10
Operating and Electrical		Full EOC	871150057523425
Power Consumption	250 W	Order code	57523425
Voltage (nom.)	230-250 V	Material no. (12 NC)	923212143801
Controls and Dimming		Local order code	IR250CHHG
Dimmable	Yes	SAP numerator – quantity per pack	1
Mechanical and Housing		EAN/UPC – Product/Case	8711500575234
Lamp Finish	Clear	Numerator – packs per outer box	10
		EAN/UPC - Case	8727900209266

InfraRed Industrial Heat Incandescent

Dimensional drawing



Product	D	C (max)
BR125 IR 250W E27 230-250V CL 1CT/10	125 mm	173 mm

