



InfraRed Industrial Heat Incandescent

BR125 IR 250W E27 230-250V CL 1CT/10


The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data

General Information		Bulb material	
Cap base	E27 [E27]	Hard Glass	
Operating position	UNIVERSAL [Any/Universal]	Luminaire Design Requirements	
Main application	Infrared Industrial	Bulb temperature (max.)	500 °C
Nominal lifetime (nom.)	5000 h	Product Data	
Operating and Electrical		Full product code	871150057523425
Power (Rated) (Nom)	250 W	Order product name	BR125 IR 250W E27 230-250V CL 1CT/10
Voltage (Nom)	230-250 V	EAN/UPC – product	8711500575234
Controls and Dimming		Order code	57523425
Dimmable	yes	Local Code	IR250CHHG
Mechanical and Housing		Numerator – quantity per pack	1
Bulb finish	Clear (CL)	Numerator – packs per outer box	10
		Material no. (12NC)	923212143801
		Net weight (piece)	104.000 g

InfraRed Industrial Heat Incandescent

Dimensional drawing



BR125 IR 250W E27 230-250V CL

Product	D	C (max)
BR125 IR 250W E27 230-250V CL 1CT/10	125 mm	173 mm

