



# SPOTONE Ring Mirror Standard

## SPOT 60W E27 240V E80 80D FR 1CT/6

Normal incandescent lamps with an internal ring-shaped parabolic aluminium mirror behind the filament


### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	80 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	E80 [E 80mm]
Product Data	
Order product name	SPOT 60W E27 240V E80 80D FR 1CT/6
Full product name	SPOT 60W E27 240V E80 80D FR 1CT/6
Full product code	871150005376310
Order code	923226545583
Material Nr. (12NC)	923226545583
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500053763
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163072029

# SPOTONE Ring Mirror Standard

## Dimensional drawing



Product	D	C (max)
SPOT 60W E27 240V E80 80D FR 1CT/6	80 mm	114.5 mm

