



# Appliance Oven P45

Appl 40W E14 230V P45 CL OV 1CT/4X5F

Lustre vacuum lamps with clear glass (P-bulb)


## Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	430 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40.0 W
Lamp Current (Nom)	0.17 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Consumption kWh/1000 h	40 kWh
Product Data	
Order product name	Appl 40W E14 230V P45 CL OV 1CT/4X5F
Full product name	Appl 40W E14 230V P45 CL OV 1CT/4X5F
Full product code	871150002933138
Order code	923265944245
Material Nr. (12NC)	923265944245
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500029331
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500390752

Appliance Oven P45

Dimensional drawing



Product	D (max)	C (max)
Appl 40W E14 230V P45 CL OV 1CT/4X5F	45 mm	75 mm

