



# Standard Lustre P45 clear

Stan 40W E27 127V P45 CL U OV 1CT/5X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

## Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	455 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	127 V
Voltage (Nom)	127 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	Stan 40W E27 127V P45 CL U OV 1CT/5X10F
Full product name	Stan 40W E27 127V P45 CL U OV 1CT/5X10F
Full product code	789440000184100
Order code	923268735892
Material Nr. (12NC)	923268735892
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400001841
Numerator - Packs per outer box	50
EAN/UPC - Case	7894400007966

Standard Lustre P45 clear

Dimensional drawing

Product	D	C (max)
Stan 40W E27 127V P45 CL U OV 1CT/5X10F	45 mm	73 mm

