



# Reflector diam 80/90/95/125 mm

## Refl 60W E27 230V NR80 25D 1CT/30

Normal incandescent lamps with an internal ring-shaped parabolic aluminium mirror behind the filament


### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	25 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR80 [NR 80mm]
Product Data	
Order product name	Refl 60W E27 230V NR80 25D 1CT/30
Full product name	Refl 60W E27 230V NR80 25D 1CT/30
Full product code	871150006581078
Order code	923331044253
Material Nr. (12NC)	923331044253
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500065810
Numerator - Packs per outer box	30
EAN/UPC - Case	8711500368959


Reflector diam 80/90/95/125 mm

Dimensional drawing



Product	D
Refl 60W E27 230V NR80 25D 1CT/30	80 mm

Photometric data



Light Distribution Diagram - Refl 60W E27 230V NR80 25D 1CT/30

