



Reflector diam 50 mm

REFL 40W E14 230V NR50 30D 1CT/30

Reflector lamps based on advanced spotlighting technology


Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal Lifetime (Nom)	1000 h
Light Technical	
Beam Angle (Nom)	30 °
Luminous Intensity (Max)	400 cd
Rated Beam Angle	30 °
Colour Rendering Index horiz (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted (FR)
Product Data	
Full product code	871150005415978
Order product name	Reflector 40W E14 230V NR50 30D 1CT/30
EAN/UPC - Product	8711500054159
Order code	05415978
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	923338544203
Net Weight (Piece)	17.100 g
ILCOS Code	IRR/F-40-230-E14-50/30

Reflector diam 50 mm


Dimensional drawing



Product	D
Reflector 40W E14 230V NR50 30D 1CT/30	50 mm

REF SPOT 40W E14 230V NR50 30D FR

Photometric data



40W NR50 30D

