



Reflector diam 50 mm

REFL 40W E14 240V NR50 30D 1CT/30

Reflector lamps based on advanced spotlighting technology


Product data

General Information	
Cap base	E14 [E14]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	1000 h
Light Technical	
Beam Angle (Nom)	30 °
Luminous intensity (max.)	400 cd
Rated beam angle	30 °
Color rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Frosted (FR)
Product Data	
Full product code	871150037986378
Order product name	Reflector 40W E14 240V NR50 30D 1CT/30
EAN/UPC – product	8711500379863
Order code	37986378
Numerator – quantity per pack	1
Numerator – packs per outer box	30
Material no. (12NC)	923338545533
Net weight (piece)	17.100 g
ILCOS Code	IRR/F-40-240-E14-50/30

Reflector diam 50 mm

Dimensional drawing



Product	D
Reflector 40W E14 240V NR50 30D 1CT/30	50 mm

REF SPOT 40W E14 240V NR50 30D FR

Photometric data

