



Reflector diam 50 mm

Reflector 40W E14 240V NR50 30D FR 1CT/6X5F

Reflector lamps based on advanced spotlighting technology

Product data

General Information	
Cap base	E14 [E14]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	1000 h

Light Technical	
Beam Angle (Nom)	30 °
Luminous intensity (max.)	400 cd
Rated beam angle	30 °
Color rendering index (nom.)	100

Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	240 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Frosted (FR)

Product Data	
Full product code	872790081029500
Order product name	Reflector 40W E14 240V NR50 30D FR 1CT/6X5F
EAN/UPC – product	8727900810295
Order code	81029500
Numerator – quantity per pack	1
Numerator – packs per outer box	30
Material no. (12NC)	923338545553
Net weight (piece)	17.100 g
ILCOS Code	IRR/F-40-240-E14-50/30

Reflector diam 50 mm

Dimensional drawing



Product	D
Reflector 40W E14 240V NR50 30D FR 1CT/6X5F	50 mm

REF SPOT 40W E14 240V NR50 30D FR

Photometric data

