



Reflector diam 50 mm

Reflector 40W E14 240V NR50 30D FR 2BC/10

Reflector lamps based on advanced spotlighting technology

Product data

General Information	
Cap base	E14 [E14]
Burning Position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	1000 h

Light Technical	
Technical Beam Angle (Nom)	30 °
Luminous intensity (max.)	400 cd
Rated beam angle	30 °
Colour Rendering Index,horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	240 V


Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Frosted (FR)

Product Data	
Full product code	872790081056100
Order product name	Reflector 40W E14 240V NR50 30D FR 2BC/10
EAN/UPC – product	8727900810578
Order code	81056100
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	923338545554
Net weight (piece)	17.100 g
ILCOS Code	IRR/F-40-240-E14-50/30

Reflector diam 50 mm

Dimensional drawing



Product	D
Reflector 40W E14 240V NR50 30D FR 2BC/10	50 mm

REF SPOT 40W E14 240V NR50 30D FR

Photometric data

