



SPOTONE Ring Mirror Spotline

REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F

Reflector lamps based on advanced spotlighting technology

Product data

General Information	
Cap base	E27 [E27]
Burning Position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	1000 h

Light Technical	
Technical Beam Angle (Nom)	30 °
Luminous intensity (max.)	420 cd
Colour Rendering Index,horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	240 V


Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Frosted (FR)

Product Data	
Full product code	871150017130600
Order product name	REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F
EAN/UPC – product	8727900844184
Order code	923339245520
Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	923339245520
Net weight (piece)	0.030 kg
ILCOS Code	IRR/F-40-240-E27-63/30

SPOTONE Ring Mirror Spotline

Dimensional drawing



Product	D
REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F	63 mm

REF SPOT 40W E27 240V NR63 30D FR

