



Reflector diam 50 mm

Refl 60W E14 230V NR50 30D 1CT/30

Reflector lamps based on advanced spotlighting technology


Product data

| General Information | |
|-----------------------------|----------------------------------|
| Cap-Base | E14 |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Beam Angle (Nom) | 30 degree(s) |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 60 W |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|-----------------------------------|
| Bulb Finish | Frosted |
| Bulb Shape | NR50 |
| Product Data | |
| Order product name | Refl 60W E14 230V NR50 30D 1CT/30 |
| Full product name | Refl 60W E14 230V NR50 30D 1CT/30 |
| Full product code | 871150038242978 |
| Order code | 923348744206 |
| Material Nr. (12NC) | 923348744206 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500382429 |
| Numerator - Packs per outer box | 30 |
| EAN/UPC - Case | 8711500391179 |

Reflector diam 50 mm

Dimensional drawing



| Product | D |
|-----------------------------------|-------|
| Refl 60W E14 230V NR50 30D 1CT/30 | 50 mm |

