



Reflector Infrared BR40, PAR38

175PAR38/HEAT/CL 120V 12/1


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

Product data

General Information		Mechanical and Housing	
Cap-Base	E26/50X39 [Skirted Medium Screw (PAR Lamps)]	Bulb Finish	Clear
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Material	Hard Glass
Nominal lifetime	5,000 hour(s)	Bulb Shape	PAR38
Rated Lifetime (Hours)	5,000 hour(s)		
Lighting Technology	Incandescent		
Light Technical		Product Data	
Color Designation	C	Order product name	175PAR38/HEAT/CL 120V 12/1
		Full product name	175PAR38/HEAT/CL 120V 12/1
		Full product code	90466771162625
		Order code	145516
		Material Nr. (12NC)	923813534608
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	046677116262
		Numerator - Packs per outer box	12
		EAN/UPC - Case	50046677145519
Operating and Electrical			
Power Consumption	175 W		
Voltage (Nom)	115-125 V		
Controls and Dimming			
Dimmable	Yes		

Reflector Infrared BR40,PAR38

Dimensional drawing



Product	D	C (max)	C1 (max)
175PAR38/HEAT/CL 120V 12/1	4-13/16 inch	5-5/16 inch	4-7/8 inch

