



Reflector Infrared BR40,PAR38

Par38 115-125V E26 1CT/12

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.


Product data

General Information	
Cap-Base	E26/50X39 [Skirted Medium Screw (PAR Lamps)]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	5,000 hour(s)
Rated Lifetime (Hours)	5,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Color Designation	C
Operating and Electrical	
Power Consumption	175 W
Wattage Equivalent	175 W
Voltage (Nom)	115-125 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	PAR38
Product Data	
Order product name	Par38 115-125V E26 1CT/12
Full product name	Par38 115-125V E26 1CT/12
Full product code	904667740518200
Order code	923813534612
Material Nr. (12NC)	923813534612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677405182
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677405187

Reflector Infrared BR40,PAR38

Dimensional drawing



Product	D	C (max)	C1 (max)
Par38 115-125V E26 1CT/12	121 mm	135 mm	123 mm

