



Halogen High Voltage SE (Theater)

6996P FWP 230V 1000W

Two distinctive features make this lamp ideal for use in theater luminaires where long life is essential. Firstly, the filament is especially designed for extended lifetime. Secondly the highly innovative P3 technology, developed by Philips, allows the pinch to better withstand extreme heat conditions which extends the average lamp lifetime, ensures consistent high-quality light output over time, and results in fewer early failures and fewer maintenance man hour costs.


Product data

General Information	
Cap-Base	GX9.5 [GX9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	900 hour(s)
Operating and Electrical	
Power Consumption	1,000 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Order product name	6996P 1000W GX9.5 230V 1CT/10
Full product name	6996P FWP 230V 1000W
Full product code	871150018493125
Order code	258046
Material Nr. (12NC)	923865143228
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500184931
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500184948

Halogen High Voltage SE (Theater)

Dimensional drawing



Product	D (max)	H	W	L	C (max)
6996P 1000W GX9.5 230V 1CT/10	15/16 inch	11/16 inch	7/16 inch	2-3/16 inch	4-3/8 inch

