



# Halogen High Voltage SE (Theater)

**6996C 1000W P28S 240V 1CT/10**

Two distinctive features make this lamp ideal for use in theater luminaires where long life is essential. Firstly, the filament is especially designed for extended lifetime. Secondly the highly innovative P3 technology, developed by Philips, allows the pinch to better withstand extreme heat conditions which extends the average lamp lifetime, ensures consistent high-quality light output over time, and results in fewer early failures and fewer maintenance man hour costs.

## Product data

General Information	
Cap base	P28S [ P28s]
Philips code	6996C
ANSI Code	FKD
LIF code	T/20 (T/14)
Operating position	UNIVERSAL [ Any or Universal (U)]
Main application	Entertainment
Life to 50% failures (nom.)	900 h
System description	P3 Technology
Light Technical	
Luminous flux (rated) (nom.)	21000 lm
Correlated colour temperature (nom.)	3050 K
Operating and Electrical	
Power (Rated) (Nom)	1000 W
Rapid-acting HBC fuse	6.3 V
Voltage (Nom)	240 V


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear (CL)
Filament shape	Bi-Plane
Filament dimensions WxH	15X13
Luminaire Design Requirements	
Pinch temperature (max.)	500 °C
Product Data	
Full product code	871150018502025
Order product name	6996C 1000W P28s 240V 1CT/10
EAN/UPC – product	8711500185020
Order code	18502025
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	923865245528

## Halogen High Voltage SE (Theater)

Net weight (piece)

0.081 kg

### Dimensional drawing



6996C 1000W P28s 240V

Product	D (max)	H	W	L	C (max)
6996C 1000W P28s 240V 1CT/10	23 mm	16 mm	10 mm	55.6 mm	125 mm

