



Broadway Studio/Film monoculot

6823P 650W GY9.5 240V 1CT/10

Two distinctive features make this lamp ideal for use in theater luminaires where long life is essential. Firstly, the filament is especially designed for extended lifetime. Secondly the highly innovative P3 technology, developed by Philips, allows the pinch to better withstand extreme heat conditions which extends the average lamp lifetime, ensures consistent high-quality light output over time, and results in fewer early failures and fewer maintenance man hour costs.


Données du produit

Informations générales	
Culot	GY9.5 [GY9.5]
Position de fonctionnement	UNIVERSEL [Libre ou universelle (U)]
Durée de vie à 50 % de mortalité (nom.)	600 h
Fonctionnement et électricité	
Consommation électrique	650 W
Tension (nom.)	240 V
Tension (nom.)	240 V
Commandes et gradation	
Variation de l'intensité lumineuse	Oui
Mécanique et boîtier	
Finition ampoule	Transparent

Données du produit	
Nom du produit de la commande	6823P 650W GY9.5 240V 1CT/10
Nom de produit complet	6823P 650W GY9.5 240V 1CT/10
Code EOC	871150018457325
Code de commande	18457325
Code 12NC	923865445528
Quantité par pack	1
Code EAN – Produit/Boîte	8711500184573
Conditionnement par carton	10
Codes EAN/UPC – Boîte	8711500184580

Broadway Studio/Film monoculot

Schéma dimensionnel



Product	D (max)	H	W	L	C (max)
6823P 650W GY9.5 240V 1CT/10	22 mm	13.5 mm	11 mm	46.5 mm	90 mm

