



# Halogen High Voltage SE (Film/Studio)

## 7389 500W GY9.5 230V 1CT/10


Halogen High Voltage SE (Film/Studio) – stars on film and video The high, constant output and consistent colour temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. What's more, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.

### Product data

General Information	
Cap-Base	GY9.5 [GY9.5]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	50 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3200 K
Operating and Electrical	
Power Consumption	500 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Order product name	7389 500W GY9.5 230V 1CT/10
Full product name	7389 500W GY9.5 230V 1CT/10
Full product code	871150018719225
Order code	923871643228
Material Nr. (12NC)	923871643228
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500187192
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500187215

# Halogen High Voltage SE (Film/Studio)

## Dimensional drawing



Product	D (max)	H	W	L	C (max)	R	K (max)	K	K (min)
7389 500W	22 mm	9 mm	10.5	36.5	75 mm	9.53	8.6 mm	7.7	7.0 mm
GY9.5 230V			mm	mm		mm		mm	
1CT/10									

