



# Halogen non-reflector

## 6605 10W G4 6V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


### Product data

General Information	
Cap-Base	G4 [ G4]
Philips Code	6605
ANSI Code	-
LIF Code	M42
Operating Position	UNIVERSAL [ Universal]
Main Application	Projection
Life to 50% Failures (Nom)	2000 h
Light Technical	
Luminous Flux (Nom)	150 lm
Correlated Color Temperature (Nom)	2700 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	10 W
Voltage (Nom)	6 V

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Filament Dimensions WxH	2.8x0.5
Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	350 °C
Product Data	
Full product code	871150041009250
Order product name	6605 10W G4 6V 1CT/10X10F
EAN/UPC - Product	8711500410092
Order code	923873910103
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	923873910103
Net Weight (Piece)	0.001 kg

## Halogen non-reflector

### Dimensional drawing



6605 10W G4 6V

Product	D (max)	L (max)	C (max)
6605 10W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm

