



# Halogen non-reflector

## 6605 10W G4 6V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

#### **Product data**


General Information		
Cap-Base	G4	
Operating Position	UNIVERSAL [Any or Universal (U)]	
Life to 50% Failures (Nom)	2,000 hour(s)	
Light Technical		
Luminous Flux	150 lm	
Correlated Color Temperature (Nom)	2700 K	
Color rendering index (CRI)	100	
Operating and Electrical		
Power Consumption	10 W	
Voltage (Nom)	6 V	
Voltage (Nom)	6 V	

Mechanical and Housing		
Bulb Material	Quartz-UV Open	
Product Data		
Order product name	6605 10W G4 6V 1CT/10X10F	
Full product name	6605 10W G4 6V 1CT/10X10F	
Full product code	871150041009250	
Order code	923873910103	
Material Nr. (12NC)	923873910103	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8711500410092	
Numerator - Packs per outer box	100	
EAN/UPC - Case	8711500423320	

Datasheet, 2024, January 18 data subject to change

## Halogen non-reflector

### Dimensional drawing



Product	D (max)	L (max)	C (max)
6605 10W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm

