

# Halogen non-reflector

## 7724I 100W GY6.35 12V

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


### Product data

| General Information                |  |
|------------------------------------|--|
| Cap-Base                           | GY6.35                                   |
| Operating Position                 | S90 [Standing +/-90D or Base Down (BDH)] |
| Life to 50% Failures (Nom)         | 2,000 hour(s)                            |
| Light Technical                    |  |
| Correlated Color Temperature (Nom) | 3200 K                                   |
| Color rendering index (CRI)        | 100                                      |
| Operating and Electrical           |  |
| Power Consumption                  | 100 W                                    |
| Voltage (Nom)                      | 12 V                                     |
| Voltage (Nom)                      | 12 V                                     |
| Mechanical and Housing             |  |
| Bulb Material                      | Quartz-UV Open                           |

| Product Data                    |                       |
|---------------------------------|-----------------------|
| Order product name              | 7724I 100W GY6.35 12V |
| Full product name               | 7724I 100W GY6.35 12V |
| Full product code               | 871150041280550       |
| Order code                      | 923875717103          |
| Material Nr. (12NC)             | 923875717103          |
| Numerator - Quantity Per Pack   | 1                     |
| EAN/UPC - Product/Case          | 8711500412805         |
| Numerator - Packs per outer box | 100                   |
| EAN/UPC - Case                  | 8711500436603         |

# Halogen non-reflector

## Dimensional drawing



| Product    | D (max) | L (min) | L (max) | L  | P (max) | P    | P (min) | C (max) |
|------------|---------|---------|---------|----|---------|------|---------|---------|
| 7724I 100W | 10.7 mm | 29.65   | 30.25   | 30 | 1.30 mm | 1.25 | 1.20 mm | 44 mm   |
| GY6.35 12V |         | mm      | mm      | mm |         | mm   |         |         |

