



# Halogen non-reflector

## 6958 250W G6.35 24V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

### Product data

General Information	
Cap-Base	G6.35 [G6.35]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	300 hour(s)

Light Technical	
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	250 W
Voltage (Nom)	24 V
Voltage (Nom)	24 V


  

Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	6958 250W G6.35 24V 1CT/10X10F
Full product name	6958 250W G6.35 24V 1CT/10X10F
Full product code	871150040989850
Order code	923882020503
Material Nr. (12NC)	923882020503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500409898
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423207

## Halogen non-reflector

### Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
6958 250W	12.5 mm	32.75	33.25	33	1.05 mm	1 mm	0.95	57 mm
G6.35 24V		mm	mm	mm			mm	
1CT/10X10F								

