



ALR 37/56 mm

GBD 20W 12V 6DEG 50PK

Delivers high lumen output and excellent color rendering for precise accent and display lighting. Philips Halogen Aluminum Reflector Lamps provide continuous color and high luminous intensity for precise accent and display lighting. These lamps offer a rated average life ranging from 2000 hours and feature excellent beam qualities for accent or ambient lighting.


Product data

General Information	
Cap-Base	BA15D [BA15d]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	6 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	235 lm
Operating and Electrical	
Power Consumption	20 W
Lamp Current (Nom)	1.67 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V

Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	R37 [R 37mm]
Approval and Application	
Energy Consumption kWh/1000 h	21 kWh
Product Data	
Order product name	GBD 20W DC Bay 12V 6D CL 1CT
Full product name	GBD 20W 12V 6DEG 50PK
Full product code	904667732840560
Order code	328401
Material Nr. (12NC)	923882717119
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677328405
Numerator - Packs per outer box	50
EAN/UPC - Case	50046677328400


ALR 37/56 mm

Dimensional drawing



Product	D (max)	C (max)
GBD 20W DC Bay 12V 6D CL 1CT	38 mm	41 mm

Photometric data



Light Distribution Diagram - GBD 20W DC Bay 12V 6D CL 1CT

