



Aluline 37/56

Alu 50W 12V R56 10D CL 1CT/10X5F

Low-voltage halogen burner in specialized aluminum reflector prevents heat in the backlight; bayonet cap for secure fitting


Product data

General Information	
Cap-Base	B15 [B15]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	10 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	760 lm
Operating and Electrical	
Power Consumption	50 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	R56 [R 56mm]
Approval and Application	
Energy Consumption kWh/1000 h	53 kWh
Product Data	
Order product name	Alu 50W 12V R56 10D CL 1CT/10X5F
Full product name	Alu 50W 12V R56 10D CL 1CT/10X5F
Full product code	871869666687600
Order code	923883917106
Material Nr. (12NC)	923883917106
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696666876
Numerator - Packs per outer box	50
EAN/UPC - Case	8718696666890

Aluline 37/56

Dimensional drawing



Product	D (max)	C (max)
Alu 50W 12V R56 10D CL 1CT/10X5F	58 mm	58 mm

Photometric data

1/1000 1/1000 1/1000

Light Distribution Diagram - Alu 50W 12V R56 10D CL 1CT/10X5F

