



Halogen High Voltage SE (Film/Studio)

6995P 1000W GX9.5 230V 1CT/10


The high, constant output and consistent color temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. Furthermore, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.

Product data

General Information	
Cap-Base	GX9.5 [GX9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	240 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3200 K
Operating and Electrical	
Power Consumption	1,000 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Full product code	871150018511225
Order product name	6995P 1000W GX9.5 230V 1CT/10
Order code	923884642928
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	923884642928
Full product name	6995P 1000W GX9.5 230V 1CT/10
EAN/UPC - Case	8711500185129
EAN/UPC - Product/Case	8711500185112

Halogen High Voltage SE (Film/Studio)

Dimensional drawing



Product	D	H	W	L	C	P	P	R	K	K
	(max)				(max)	(max)	(min)		(max)	(min)
6995P	23 mm	14.5	11	55	110	3.25	3.10	9.53	9.2	8.4
1000W		mm	mm	mm	mm	mm	mm	mm	mm	mm
GX9.5										
230V										
1CT/10										

