



HalogenA IDE

HALA IDE 500W E40 230V CL 1CT/6

Mains-voltage high-wattage double-envelope giving a white halogen light

Product data

General Information	
Cap-Base	E40 [E40]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal Lifetime (Nom)	2000 h
Switching Cycle	8000X

Light Technical	
Luminous Flux (Nom)	10250 lm
Luminous Flux (Rated) (Nom)	10250 lm
Colour Temperature, horizontal (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	20.5 lm/W
Colour Rendering Index horiz (Nom)	100
LLMF at End of Nominal Lifetime (Min)	80 %

Operating and Electrical	
Power (Rated) (Nom)	500.0 W
Lamp Current (Nom)	2.17 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear (CL)

Approval and Application	
Energy Efficiency Label	D
Energy Consumption kWh/1000 h	500 kWh

Product Data	
Full product code	871150049126810
Order product name	HalogenA IDE 500W E40 230V CL 1CT/6
EAN/UPC - Product	8711500491268
Order code	49126810
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	923900144240
Net Weight (Piece)	141.000 g
ILCOS Code	HEGT-500-230-e40

HalogenA IDE

Dimensional drawing



Product	D (max)	C (max)
HalogenA IDE 500W E40 230V CL 1CT/6	38.5 mm	216 mm

IDE 500W E40 230V T38 CL

