



HalogenA IDE

HALA IDE 1000W E40 230V CL 1CT/6

Mains-voltage high-wattage double-envelope giving a white halogen light

Product data

| General Information | |
|------------------------|----------------------------------|
| Cap-Base | E40 [E40] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2,000 hour(s) |
| Switching Cycle | 8,000 |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Halogen |

| Light Technical | |
|------------------------------------|-----------|
| Luminous Flux | 24,000 lm |
| Correlated Color Temperature (Nom) | 2900 K |
| Luminous Efficacy (rated) (Nom) | 24 lm/W |
| Color rendering index (CRI) | 100 |

| Operating and Electrical | |
|---------------------------|----------------------|
| Power Consumption | 1,000.0 W |
| Lamp Current (Nom) | 4.35 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |


| Mechanical and Housing | |
|------------------------|--------------|
| Bulb Finish | Clear |
| Bulb Shape | T38 [T 38mm] |

| Approval and Application | |
|-------------------------------|----------|
| Energy Consumption kWh/1000 h | 1000 kWh |

| Product Data | |
|---------------------------------|----------------------------------|
| Order product name | HALA IDE 1000W E40 230V CL 1CT/6 |
| Full product name | HALA IDE 1000W E40 230V CL 1CT/6 |
| Full product code | 871150049128210 |
| Order code | 49128210 |
| Material Nr. (12NC) | 923900244240 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500491282 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8711500499967 |

HalogenA IDE

Dimensional drawing



| Product | D (max) | C (max) |
|----------------------------------|---------|---------|
| HalA IDE 1000W E40 230V CL 1CT/6 | 38.5 mm | 256 mm |

