



# HalogenA IDE

## HALA IDE 1000W E40 230V CL 1CT/6

Mains-voltage high-wattage double-envelope giving a white halogen light


### Product data

General Information	
Cap-Base	E40 [ E40]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Nominal Lifetime (Nom)	2000 h
Switching Cycle	8000X
Light Technical	
Luminous Flux (Nom)	24000 lm
Luminous Flux (Rated) (Nom)	24000 lm
Colour Temperature, horizontal (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	24 lm/W
Colour Rendering Index horiz (Nom)	100
LLMF at End of Nominal Lifetime (Min)	80 %
Operating and Electrical	
Power (Rated) (Nom)	1000.0 W
Lamp Current (Nom)	4.35 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear (CL)
Approval and Application	
Energy Efficiency Label	C
Energy Consumption kWh/1000 h	1000 kWh
Product Data	
Full product code	871150049128210
Order product name	HalogenA IDE 1000W E40 230V CL 1CT/6
EAN/UPC - Product	8711500491282
Order code	49128210
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	923900244240
Net Weight (Piece)	158.000 g
ILCOS Code	HEGT-1000-230-e40

# HalogenA IDE

## Dimensional drawing



Product	D (max)	C (max)
HalogenA IDE 1000W E40 230V CL 1CT/6	38.5 mm	256 mm

IDE 1000W E40 230V T38 CL

