



HalogenA IDE

HaIA IDE 1000W E40 230V CL 1CT/6

Mains-voltage high-wattage double-envelope giving a white halogen light


Product data

General Information	
Cap-Base	E40 [E40]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	24,000 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	24 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	1,000.0 W
Lamp Current (Nom)	4.35 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T38 [T 38mm]
Approval and Application	
Energy Consumption kWh/1000 h	1000 kWh
Product Data	
Order product name	HaIA IDE 1000W E40 230V CL 1CT/6
Full product name	HaIA IDE 1000W E40 230V CL 1CT/6
Full product code	87115004912810
Order code	923900244240
Material Nr. (12NC)	923900244240
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500491282
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500499967

HalogenA IDE

Dimensional drawing



Product	D (max)	C (max)
HalA IDE 1000W E40 230V CL 1CT/6	38.5 mm	256 mm

