



鹵素反射燈

6423 150W GZ6.35 15V 1CT/10X5F

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

产品数据

基本資訊	
接口	GZ6.35 [GZ6.35]
Philips 代碼	6423
Ansi 代碼	EFR
LIF 代碼	A1/232
操作位置	P90/P15
主要應用	Projection
至 50% 故障的使用時間 (標稱)	50 h
照明科技	
相關色溫 (標稱)	3380 K
演色性指數 (標稱)	100
運作和電氣	
Power (Rated) (Nom)	150 W


電壓 (標稱)	15 V
控制調光	
可調光	Yes
機械和殼體	
燈泡材質	Quartz-UV Open
反射罩表層	光滑
燈絲尺寸 (寬 x 高)	-
燈具設計要求	
燈泡溫度 (最大)	900 °C
尖端溫度 (最大)	400 °C
作業距離 WD	32 mm

鹵素反射燈

產品參數	
完整產品碼	871150042733560
訂購產品名稱	6423 150W GZ6.35 15V 1CT/10X5F
EAN/UPC - 產品	8711500427335
訂購代碼	923916818504
分子 - 各件數量	1

分子 - 每一外盒內件數	50
材質編號(12NC)	923916818504
淨重 (件)	0.023 kg

二维绘图



6423 150W GZ6.35 15V

Product	D (max)	C (max)
6423 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

