



# Plusline Compact

## Plusline C 150W R7s 230V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light


### Product data

General Information	
Cap base	R7S [ R7s]
Burning Position	UNIVERSAL [ Any/Universal]
Nominal lifetime (nom.)	2000 h
Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	2400 lm
Lamp Luminous Efficacy EM (Nom)	16 lm/W
Colour Rendering Index,horiz (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	150 W
Lamp current (nom.)	0.65 A
Starting time (nom.)	0.0 s
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Bulb finish	Clear (CL)
Cap base information	10

Approval and Application	
Energy efficiency label (EEL)	D
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	872790080887200
Order product name	Plusline C 150W R7s 230V 1CT/10X10F
EAN/UPC – product	8727900808872
Order code	923919943202
Local Code	PLUSLINE150W23
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	923919943202
Net weight (piece)	0.005 kg
ILCOS Code	HDG//RS-150-230-R7s-74,9

## Plusline Compact

### Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline C 150W R7s 230V 1CT/ 10X10F	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

DEComp 150W R7s 230V T3 CL

