



Plusline Compact

Plusline C 100W R7s 230V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light

Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	1,550 lumen
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	15.5 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Lamp Current (Nom)	0.43 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]
Product Data	
Full product code	872790080839100
Order product name	Plusline C 100W R7s 230V 1CT/10X10F
Order code	923920043242
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	923920043242
Full product name	Plusline C 100W R7s 230V 1CT/10X10F
EAN/UPC - Case	8727900808407
EAN/UPC - Product/Case	8727900808391

Plusline Compact

Dimensional drawing

Product	D (max)	B (max)	B	B (min)	C (max)
Plusline C 100W R7s 230V 1CT/10X10F	12 mm	76.5 mm	74.9 mm	73.3 mm	78 mm

