



Halogen reflector

13096 ELH 300W GY5.3 120V 1CT/24

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

Product data

General Information	
Cap base	GY5.3 [GY5.3]
Operating position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% failures (nom.)	35 h
Light Technical	
Colour rendering index (CRI)	100
Operating and Electrical	
Power Consumption	300 W
Voltage (nom.)	120 V
Voltage (nom.)	120 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb material	Quartz-UV Open

Reflector finish	Faceted reflector
Product Data	
Order product name	13096 ELH 300W GY5.3 120V 1CT/24
Full product name	13096 ELH 300W GY5.3 120V 1CT/24
Full EOC	871150041057330
Order code	41057330
Material no. (12 NC)	923920936394
Local order code	ELH
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500410573
Numerator – packs per outer box	24
EAN/UPC – Case	8711500419057

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
13096 ELH 300W GY5.3 120V 1CT/24	50.7 mm	44.5 mm

