



# Halogen reflector

## 13096 ELH 300W GY5.3 120V 1CT/24

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

### Product data

| General Information         |  |
|-----------------------------|--|
| Cap-Base                    | GY5.3 [GY5.3]                            |
| Operating Position          | S90 [Standing +/-90D or Base Down (BDH)] |
| Life to 50% Failures (Nom)  | 35 hour(s)                               |
| Light Technical             |  |
| Color rendering index (CRI) | 100                                      |
| Operating and Electrical    |  |
| Power Consumption           | 300 W                                    |
| Voltage (Nom)               | 120 V                                    |
| Voltage (Nom)               | 120 V                                    |
| Controls and Dimming        |  |
| Dimmable                    | Yes                                      |
| Mechanical and Housing      |  |
| Bulb Material               | Quartz-UV Open                           |

| Reflector Finish                | Facetted reflector               |
|---------------------------------|----------------------------------|
| Product Data                    |                                  |
| Order product name              | 13096 ELH 300W GY5.3 120V 1CT/24 |
| Full product name               | 13096 ELH 300W GY5.3 120V 1CT/24 |
| Full product code               | 871150041057330                  |
| Order code                      | 923920936394                     |
| Material Nr. (12NC)             | 923920936394                     |
| Local order code                | 13096                            |
| Numerator - Quantity Per Pack   | 1                                |
| EAN/UPC - Product/Case          | 8711500410573                    |
| Numerator - Packs per outer box | 24                               |
| EAN/UPC - Case                  | 8711500419057                    |

# Halogen reflector

## Dimensional drawing



| Product                          | D (max) | C (max) |
|----------------------------------|---------|---------|
| 13096 ELH 300W GY5.3 120V 1CT/24 | 50.7 mm | 44.5 mm |

