



Halogen reflector

5995 EJM 150W GX5.3 21V 1CT/24

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

Product data


General information		Voltage (Nom)	
Cap base	GX5.3 [GX5.3]	21 V	
Philips code	5995	Controls and dimming	
ANSI Code	EJM	Dimmable	Yes
LIF Code	-	Mechanical and housing	
Operating position	S90 [Standing +/-90D or Base Down (BDH)]	Bulb material	Quartz-UV Open
Main application	Projection	Reflector finish	Smooth
Life to 50% failures (nom.)	40 h	Filament dimensions WxH	-
Light technical		Luminaire design requirements	
Luminous flux (rated) (nom.)	1200 lm	Bulb temperature (max.)	900 °C
Colour rendering index (nom.)	100	Pinch temperature (max.)	400 °C
		Pinch Temperature (Max)-DUP(do not use)	400 °C
Operating and electrical		Working distance WD	38 mm
Power (Rated) (Nom)	150 W		

Halogen reflector

Product data	
Full product code	871150041063430
Order product name	5995 EJM 150W GX5.3 21V 1CT/24
EAN/UPC – product	8711500410634
Order code	41063430
SAP numerator – quantity per pack	1

Local code description	EJM 21V 150W 24 PACK
Numerator – packs per outer box	24
SAP material	923921019894
Net Weight (Piece)	0.025 kg

Dimensional drawing



5995 EJM 150W GX5.3 21V 1CT/24

Product	D (max)	C (max)
5995 EJM 150W GX5.3 21V 1CT/24	50.7 mm	44.5 mm

