



Halogen reflector

EJM 21V 150W 24 PACK

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

Product data

General Information		Voltage (Nom)	
Base	GX5.3 [GX5.3]	21 V	
Philips Code	5995	Controls and Dimming	
ANSI Code	EJM	Dimmable	Yes
LIF Code	-	Mechanical and Housing	
Operating Position	Base Down +/- 90 D [Base Down +/- 90 D]	Bulb Material	Quartz-UV Open
Main Application	Projection	Reflector Finish	Smooth
Life to 50% Failures (Nom)	40 h	Filament Dimensions WxH	-
Light Technical		Luminaire Design Requirements	
Luminous Flux (Rated) (Nom)	1200 lm	Bulb Temperature (Max)	900 °C
Correlated Color Temperature (Nom)	3400 K	Pinch Temperature (Max)	400 °C
Color Rendering Index (Nom)	100	Working Distance WD	38 mm
Operating and Electrical			
Power (Rated) (Nom)	150 W		


Halogen reflector

Product Data

Order product name	5995 EJM 150W GX5.3 21V 1CT/24
EAN/UPC - Product	8711500410634
Order code	239426
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	24
Material Nr. (12NC)	923921019894
Net Weight (Piece)	0.025 kg

Dimensional drawing



5995 EJM 150W GX5.3 21V

Product	D (max)	C (max)
5995 EJM 150W GX5.3 21V 1CT/24	50.7 mm	44.5 mm

