



Halogen reflector

14501 150W GX5.3 20V

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

Product data

General Information	
Cap-Base	GX5.3 [GX5.3]
Operating Position	S105 [s105]
Life to 50% Failures (Nom)	500 hour(s)

Light Technical	
Correlated Color Temperature (Nom)	3150 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	20 V
Voltage (Nom)	20 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Facetted reflector
Bulb Shape	R50 [R 50mm]

Product Data	
Order product name	DDL 150W 20V 24PK
Full product name	14501 150W GX5.3 20V
Full product code	871150041061030
Order code	41061030
Material Nr. (12NC)	923921419794
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410610

Halogen reflector

Numerator - Packs per outer box	24
EAN/UPC - Case	8711500419002

Dimensional drawing



Product	D (max)	C (max)
DDL 150W 20V 24PK	50.7 mm	44.5 mm

