



Halogen reflector

14501 150W GX5.3 20V

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

Product data

General Information	
Cap base	GX5.3 [GX5.3]
Philips code	14501
ANSI Code	DDL
LIF Code	-
Operating position	S105 [s105]
Main application	Projection
Life to 50% failures (nom.)	500 h
J code	-

Light Technical	
Luminous flux (rated) (nom.)	400 lm
Correlated Colour Temperature (Nom)	3150 K
Colour rendering index (nom.)	100

Operating and Electrical	
Power (Rated) (Nom)	150 W
Voltage (Nom)	20 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Cap-base information	na [-]
Bulb material	Quartz-UV Open
Reflector finish	Facetted
Filament shape	-
Filament dimensions WxH	-
Bulb shape	R50 [R 50mm]

Halogen reflector

Luminaire Design Requirements


Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Working distance WD	165 mm

Product Data

Full product code	871150041061030
Order product name	DDL 150W 20V 24PK

EAN/UPC – product	8711500410610
Order code	41061030
SAP numerator – quantity per pack	1
Numerator – packs per outer box	24
SAP material	923921419794
SAP net weight (piece)	0.026 kg

Dimensional drawing



14501 150W GX5.3 20V

Product	D (max)	C (max)
DDL 150W 20V 24PK	50.7 mm	44.5 mm

