



Halogen non-reflector

5761 30W G4 6V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


Product data

General Information	
Cap base	G4 [G4]
Philips code	5761
ANSI Code	-
LIF code	-
Operating position	UNIVERSAL [Any or Universal (U)]
Main application	Projection
Life to 50% failures (nom.)	100 h
Light Technical	
Luminous flux (nom.)	765 lm
Correlated colour temperature (nom.)	3200 K
Color rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	30 W
Voltage (Nom)	6 V

Mechanical and Housing	
Bulb material	Quartz-UV Open
Filament dimensions WxH	1.6x1.6
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	400 °C
Product Data	
Full product code	871150041084950
Order product name	5761 30W G4 6V 1CT/10X10F
EAN/UPC – product	8711500410849
Order code	41084950
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	923931110103
Net weight (piece)	0.001 kg

Halogen non-reflector

Dimensional drawing



5761 30W G4 6V

Product	D (max)	L (max)	C (max)
5761 30W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm

