



# Plusline Large (double ended)

## Plusline L 1000W R7s 230V 1CT/10


PlusLine Large flood delivers maximum light output to light up large areas like outdoor, buildings and shops.

### Product data

General Information		Controls and Dimming	
Cap-Base	R7s	Dimmable	Yes
Operating Position	P4 [Parallel +/-4D or Horizontal(HOR)]		
Nominal lifetime	2,000 hour(s)	Mechanical and Housing	
Switching Cycle	8,000	Bulb Finish	Clear
Rated Lifetime (Hours)	2,000 hour(s)	Bulb Shape	T11
Lighting Technology	Halogen		
Light Technical		Approval and Application	
Luminous Flux	21,500 lm	Energy Consumption kWh/1000 h	1000 kWh
Correlated Color Temperature (Nom)	2900 K		
Luminous Efficacy (rated) (Nom)	21.5 lm/W	Product Data	
Color rendering index (CRI)	100	Order product name	Plusline L 1000W R7s 230V 1CT/10
Operating and Electrical		Full product name	Plusline L 1000W R7s 230V 1CT/10
Power Consumption	1,000 W	Full product code	871150049434401
Lamp Current (Nom)	4.35 A	Order code	923932143203
Starting Time (Nom)	0.0 s	Material Nr. (12NC)	923932143203
Warm-up time to 60% light	instant full light s	Numerator - Quantity Per Pack	1
Power Factor (Fraction)	1	EAN/UPC - Product/Case	8711500494344
Voltage (Nom)	230 V	Numerator - Packs per outer box	10
Voltage (Nom)	230 V	EAN/UPC - Case	8718291720812

Plusline Large (double ended)

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1000W R7s 230V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm

