



# Plusline Large

## Plusline L 1000W R7s 230V 1CT/10

Mains-voltage linear lamp giving white halogen light


### Product data

General Information	
Cap base	R7S [ R7s]
Burning Position	P4 [ Parallel +/-4D or Horizontal(HOR)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8000X
Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	21500 lm
Lamp Luminous Flux (Nom)	21500 lm
Colour Temperature, horizontal (Nom)	2900 K
Lamp Luminous Efficacy EM (Nom)	21.5 lm/W
Colour Rendering Index,horiz (Nom)	100
LLMF at end of nominal lifetime (min.)	80 %
Operating and Electrical	
Power (Rated) (Nom)	1000 W
Lamp current (nom.)	4.35 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy efficiency label (EEL)	C
Energy Consumption kWh/1000 h	1000 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	872790080851300
Order product name	Plusline L 1000W R7s 230V 1CT/10
EAN/UPC – product	8727900808513
Order code	923932143241
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	923932143241
Net weight (piece)	0.016 kg
ILCOS Code	HDG//RS-1000-230-R7s-185,7

## Plusline Large

### Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1000W R7s 230V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm

DEBig 1000W R7s 230V T11 CL

