



Plusline Large (double ended)

Plusline L 1500W R7s 230V 1CT/10


PlusLine Large flood delivers maximum light output to light up large areas like outdoor, buildings and shops.

Product data

General Information		Controls and Dimming	
Cap-Base	R7s	Dimmable	Yes
Operating Position	P4 [Parallel +/-4D or Horizontal(HOR)]	Mechanical and Housing	
Nominal lifetime	2,000 hour(s)	Bulb Finish	Clear
Switching Cycle	8,000	Bulb Shape	T11
Rated Lifetime (Hours)	2,000 hour(s)	Approval and Application	
Lighting Technology	Halogen	Energy Consumption kWh/1000 h	1500 kWh
Light Technical		Product Data	
Luminous Flux	33,000 lm	Order product name	Plusline L 1500W R7s 230V 1CT/10
Correlated Color Temperature (Nom)	2900 K	Full product name	Plusline L 1500W R7s 230V 1CT/10
Luminous Efficacy (rated) (Nom)	22 lm/W	Full product code	871150049435101
Color rendering index (CRI)	100	Order code	923932243203
Operating and Electrical		Material Nr. (12NC)	923932243203
Power Consumption	1,500.0 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	6.52 A	EAN/UPC - Product/Case	8711500494351
Starting Time (Nom)	0.0 s	Numerator - Packs per outer box	10
Warm-up time to 60% light	instant full light s	EAN/UPC - Case	8718291720836
Power Factor (Fraction)	1		
Voltage (Nom)	230 V		
Voltage (Nom)	230 V		

Plusline Large (double ended)

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1500W R7s 230V 1CT/10	11 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm

